

FAST SANDING OF PAINT AND WOOD

EXPERT C470 Sandpaper

EXPERT

- ① Exceptional abrasion with Bosch Surface Structure
- ② Grain alignment during production ensures aggressive cut
- ③ Grain distribution optimised for high-speed sanding



* vs. Bosch C420



BOSCH

EXPERT C470 SANDING ROLL



- ▶ Ideal for highly effective fast sanding of flat surfaces; to remove old paint; or to smooth, prepare and finish surfaces
- ▶ EXPERT Abrasives - the very best for all trades
- ▶ Up to 2x faster than Bosch C420 Sandpaper
- ▶ Clamp it on



PRODUCT PROPERTIES				ORDERING INFORMATION				
Roll width mm	Roll length m	Grit	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number	
5 m	93	5	40	P1f	1	1	542 409	2 608 900 902
50 m	93	50	40	P0f	1	1	543 062	2 608 900 968
5 m	93	5	60	P1f	1	1	542 416	2 608 900 903
50 m	93	50	60	P0f	1	1	543 079	2 608 900 969
5 m	93	5	80	P1f	1	1	542 423	2 608 900 904
50 m	93	50	80	P0f	1	1	543 086	2 608 900 970
	93	50	100	P0f	1	1	543 093	2 608 900 971
5 m	93	5	120	P1f	1	1	542 430	2 608 900 905
50 m	93	50	120	P0f	1	1	543 109	2 608 900 972
5 m	93	5	180	P1f	1	1	542 447	2 608 900 906
50 m	93	50	180	P0f	1	1	543 116	2 608 900 973
5 m	93	5	240	P1f	1	1	542 454	2 608 900 907
50 m	93	50	240	P0f	1	1	543 123	2 608 900 974
	93	50	320	P0f	1	1	543 130	2 608 900 975
	93	50	400	P0f	1	1	543 147	2 608 900 976
5 m	115	5	40	P1f	1	1	542 348	2 608 900 896
50 m	115	50	40	P0f	1	1	543 154	2 608 900 977
5 m	115	5	60	P1f	1	1	542 355	2 608 900 897



BOSCH

EXPERT C470 SANDING ROLL

PRODUCT PROPERTIES				ORDERING INFORMATION				Part number
Roll width mm	Roll length m	Grit	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...		
50 m	115	50	60	P0f	1	1	543 161	2 608 900 978
5 m	115	5	80	P1f	1	1	542 362	2 608 900 898
50 m	115	50	80	P0f	1	1	543 178	2 608 900 979
	115	50	100	P0f	1	1	543 185	2 608 900 980
5 m	115	5	120	P1f	1	1	542 379	2 608 900 899
50 m	115	50	120	P0f	1	1	543 192	2 608 900 981
5 m	115	5	180	P1f	1	1	542 386	2 608 900 900
50 m	115	50	180	P0f	1	1	543 208	2 608 900 982
5 m	115	5	240	P1f	1	1	542 393	2 608 900 901
50 m	115	50	240	P0f	1	1	543 215	2 608 900 983
	115	50	320	P0f	1	1	543 222	2 608 900 984
	115	50	400	P0f	1	1	543 239	2 608 900 985



BOSCH