

Backpack Vacuum Cleaner LXT®

DVC261

18V X2, 110 mbar, 2 l

Efficient machine-connectable backpack vacuum cleaner for cleaning or dust removal

A backpack vacuum cleaner with an adjustable harness and waist strap to make mobile work lighter. Efficient HEPA filter and 2L dust bag. Three power settings and separate LED light.



18V 18V → 36V LXT BL MOTOR HEPA filter

Technical specifications

Nominal Battery Voltage	2 x 18 V
Voltage LXT	✓
Brushless Motor	✓
Air volume	2,3 m³/min
Max. sealed suction	110 mbar
Vacuum hose length	1,0 m
Vacuum hose diameter	28 mm
Dust Bag Capacity	2,0 L
Sound Pressure Level (L _{pA})	≤ 70 dB(A)
Noise Uncertainty (K Factor)	2,5 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s²
Vibration Uncertainty (K Factor)	1,5 m/s²
Tool weight with battery	3,8 - 4,5 kg
Product Dimensions (L x W x H):	230 x 152 x 373 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	3000 - 8500 min ⁻¹

User benefits

- 36V performance from two 18V batteries connected in series. The batteries are placed in parallel in separate battery docking stations.
- Brushless maintenance-free and long-life motor
- HEPA filter removes particles with an efficiency rating of 99.75%
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Optional AC

126756-8

Bent Pipe Assembly



127093-3

Bent Pipe



140G19-0

Aluminium telescopic pipe with pipe



140H94-2

Soft Brush 360 Complete Set, Blue



140H95-0

Seat Nozzle, Ø32 Mm



191G86-8

Nozzle assembly set



191M30-1

Brush Nozzle



195433-3

Hose Ø 28 mm x 3,5 m



195547-8

Adapter 22 / 25 mm



197901-2

Flexible rubber nozzle



198532-0

Nozzle assembly 320 mm



199041-2

Seat nozzle set



199493-7

Hose complete Ø 32 mm x 1700 mm



422437-5

Rubber Crevice Nozzel 330 x Ø35



451244-9

Plastic Straight Pipe 28 x 465 mm,



Other

User manual

Parts drawing