

Datasheet

Stock No: 137-3860

RS Pro 1.75mm Black Rubber Cable Sleeve, 20mm Length



Image representative of range

Product Details

High Temperature Expandable Sleeves

Manufactured from highly elastic black chloroprene

Operating temperature -30 to 90°C (+110°C for short time periods)

Flame retardant to UL94 V-0

Good mechanical properties, resistance to ozone, aromatic fuels, moisture and oil

Breaking strain	600%
Resistivity	$4 \times 10^9 \Omega m$
Dielectric strength	13kV
Operating temperature	-30°C to +130°C
Flame retardant	UL94V-0

Expandable Sleeving

Specifications

Sleeve Diameter	1.75mm
Colour	Black
Material	Neoprene
Sleeve Length	20mm
Minimum Cable Diameter	1.75mm
Maximum Cable Diameter	3.5mm
Dielectric Strength	13kV/mm
Wall Thickness	0.5mm