


PRODUCT PROFILE

edding 1800 profipen



Product text

- Precision fineliner for writing and precise sketching on light-coloured paper
- The metal-framed plastic nib is available in stroke widths of 0.25 mm, 0.35 mm, 0.5 mm, 0.7 mm
- The pigment ink is waterproof and extremely lightfast
- Available in the colours black, red, blue and green

Target group

- Users in companies, authorities, schools and universities
- Architects, engineers and designers for technical drawing
- Mainly women who like to be creative and to create results with an individual touch (e.g. decoration)
- Hobby crafters who seek inspiration as well as reliable products - when crafting for themselves or with children

Benefits for the consumer

- Easy and clean to use for uncomplicated, spontaneous creativity
- Cap with practical metal clip - can be stored on end of barrel
- The cap has a high-quality stainless steel clip
- High-quality brand product

Product Information

Product ingredients

Water based ink

- Yes

Dye based ink

- Yes

Excluded additives

- nothing to be mentioned

Product features

Shape of nib

- round

Stroke width

- 0,25-0,7 mm

Neutral smell

- Yes

Waterproof

- Yes

Smudge-proof

- Yes

Lightfast

- Yes

Quick-drying

- Yes

Special ink prevents bleeding through the paper

- Yes

Applicable on

- Paper

Cap can be repositioned

- Yes

Has clip

- Yes

Suitable for stencils

- Yes

Product material

Product material of cap

- PP

Product material of clip

- Stainless steel

Product material of barrel

- PP

Product material of plug

- PP

Product material of nib

- Plastic

Product material of filter

- Polyester

Colour

Colour range of product (number of colours)

- 4

Colour range of product

- 001-004

- | | |
|--|--------|
| Colour of cap | • 003 |
| Colour of cap - name | • blue |
| Colour of barrel | • 003 |
| Colour of barrel - name | • blue |
| Communication of writing colour by cap | • Yes |

	SAP no.	KEA / order no.
Single product	2400XXX	4-180001XXX
Blister of 1	8265XXX	4-180001-1-1XXX
Set of 3 001 black (3x 001)	3406001	4-1800-3

EAN code				
	Single product	Folding box	Outer carton	Shipping carton
001 black	4004764043859	4004764441686	4004764466184	4004764089093
002 red	4004764043866	4004764441693	4004764466191	4004764089109
003 blue	4004764043873	4004764441709	4004764466207	4004764089116
004 green	4004764043880	4004764441716	4004764466214	4004764089123
001 black	4004764044108	4004764441747	4004764466245	4004764089147
002 red	4004764044115	4004764441754	4004764466252	4004764089154
003 blue	4004764044122	4004764441761	4004764466269	4004764089161
004 green	4004764044139	4004764441778	4004764466276	4004764089178
001 black	4004764044351	4004764441808	4004764466306	4004764089185
002 red	4004764044368	4004764441815	4004764466313	4004764089192
003 blue	4004764044375	4004764441822	4004764466320	4004764089208
004 green	4004764044382	4004764441839	4004764466337	4004764089215
001 black	4004764325726	4004764440740	4004764465248	4004764089239
002 red	4004764325733	4004764440757	4004764465255	4004764089246
003 blue	4004764325740	4004764440764	4004764465262	4004764089253
004 green	4004764325757	4004764440771	4004764465279	4004764089260
Blister of 1 001 black	4004764061686	-	4004764061693	4004764061709
Blister of 1 001 black	4004764061716	-	4004764061723	4004764061730
Blister of 1 001 black	4004764061747	-	4004764061754	4004764061761
Set of 3 001 black (3x 001)	4004764044603	-	4004764100668	4004764491360

Packaging					
	Net weight	Folding box	Outer carton	Shipping carton	Pallet
Single product	8,8 g	10 pcs	100 pcs	1.200 pcs	28.800 pcs
Blister of 1	8,8 g	-	10 pcs	100 pcs	3.200 pcs
Set of 3 001 black (3x 001)	27 g	1 pcs	25 pcs	300 pcs	7.200 pcs