

Features

- Replacement blade to part no. TPP-TR-6000-R pneumatic side cutter.
- Flush cut.
- Maximum cutting capacity Ø 1.60 mm copper wire.
- Blades are made in Italy from a special steel
- Blade steel thickness 6 mm.
- Made in Italy.

RS PRO Blade for Pneumatic Side Cutter (replacement)

RS Stock No.: (0429711)



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Replacement blade for the pneumatic side cutter 0429709.
- Easily exchangeable replacement blade.
- Suitable for cutting conventional components.
- Maximum cutting capacity $\varnothing$ 1.60 mm copper wire.
- Blades are made in Italy from a special steel.
- Blade steel thickness 6 mm.
- Made in Italy.

General Specifications

Cutter Type	flush cutter
Tip Style	20° angled flush cutter
Blade Material	Tempered high carbon steel

Mechanical Specifications

Cutting capacities	$\varnothing$ 1.60mm (14 awg) copper wire
Cutting force	90 kg
Blade Steel thickness	6mm
Blade angle	20°

