



MECCA PRO 1/2" IMPACT SOCKET SET DIN 22 PIECES

- 18 regular metric sockets from 10 to 32 mm
- Retaining pins (2 pcs) and rings (2 pcs) included
- Made of chrome molybdenum (CR-MO)
- For use with power tools
- Supplied in a robust blow moulded box
- Designed and manufactured to DIN3129

Impact Socket Set 1/2" Drive mm DIN 22 Pieces

General information

Country of origin: Taiwan
Barcode: 5020385020382
Tarriff code Europe: 8204200000
ECCN US: EAR99
UNSPSC: 27111703

Dimensions

Net weight (g): 3456
Width (mm): 369
Depth (mm): 185
Height (mm): 85

Attributes

Product type: Impact Tool Sets
Certificates: N/A
Number of pieces: 22
Drive: 1/2"
Socket type: Regular, 6-point
Standard type: DIN
Unit of measurement: Metric

Features



Technical changes and errors may occur. 01-08-2024 19:57



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
 441 39 Alingsås, Sweden

LIST OF CONTENTS



T9222 MECCA PRO 1/2" Impact Socket Set DIN 22 Pieces

920510N	1/2" Impact Socket DIN Metric 10 mm
920511N	1/2" Impact Socket DIN Metric 11 mm
920512N	1/2" Impact Socket DIN Metric 12 mm
920513N	1/2" Impact Socket DIN Metric 13 mm
920514N	1/2" Impact Socket DIN Metric 14 mm
920515N	1/2" Impact Socket DIN Metric 15 mm
920516N	1/2" Impact Socket DIN Metric 16 mm
920517N1	1/2" Impact Socket DIN Metric 17 mm
920518N	1/2" Impact Socket DIN Metric 18 mm
920519N1	1/2" Impact Socket DIN Metric 19 mm
920521N1	1/2" Impact Socket DIN Metric 21 mm
920522N	1/2" Impact Socket DIN Metric 22 mm
920524N	1/2" Impact Socket DIN Metric 24 mm
920527N	1/2" Impact Socket DIN Metric 27 mm
920528N	1/2" Impact Socket DIN Metric 28 mm
920529N	1/2" Impact Socket DIN Metric 29 mm
920530N	1/2" Impact Socket DIN Metric 30 mm
920532N	1/2" Impact Socket DIN Metric 32 mm
O92194	Retaining Ring 19 × 4.0 mm
O92244	Retaining Ring 24 × 4.0 mm
P92320	Retaining Pin 3 × 20 mm
P92325	Retaining Pin 3 × 25 mm