


Check valve VBNF-CBA-Q4-Q4

Part number: 8193271

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Valve function	Non-return function
Pneumatic connection, port 1	QS-4
Pneumatic connection, port 2	QS-4
Pilot air port 21	QS-4
Type of actuation	Manual
Standard nominal flow rate (standardised to DIN 1343)	120 l/min
Operating pressure	≤1 MPa
Operating pressure	≤10 bar
Pilot pressure	0.2 MPa ... 1 MPa
Pilot pressure	2 bar ... 10 bar
Pilot pressure	29 psi ... 145 psi
Ambient temperature	-10 °C ... 60 °C
Material housing	PBT
Housing colour	grey
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Mounting position	optional
Type act., cont. n.-r. func.	Pneumatic
Manual exhaust function	Non-detenting
Symbol	00991957
Operating pressure complete temperature range	0.2 bar ... 10 bar
Standard flow rate 1→2 (6-0)	210 l/min
Standard nominal flow rate 1→2 (6-5)	130 l/min
Switching time off	9 ms
Switching time on	6 ms
Explosion protection	Zone 2 (ATEX) Zone 22 (ATEX)
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C ... 70 °C
Media temperature	-10 °C ... 60 °C
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Product weight	23.8 g
Material covering	ES-BE
Note on materials	RoHS-compliant

Feature	Value
Material cover	PBT
Material seals	NBR
Material release ring	POM