

8501NR61

Plug in relay, Type N, relay socket, 11 tubular pin, single tier, for 8510KP relays and 9050JCK timers



Main

Product range	8501N
Product type	Relay Socket
Pin shape	Tubular
Number of pins	11
[In] rated current	15 A 300 V AC 5 A 600 V AC

Complementary

Electrical connection	Single tiered screw clamp terminals
Mounting type	Panel DIN rail
Package quantity	1

Environment

Certifications	UL Recognized[RETURN]CSA[RETURN]CE
Height	2.16 in (54.8 mm)
Width	2.32 in (59 mm)
Depth	0.97 in (24.6 mm)

Ordering and shipping details

Category	21142-8501 N
Discount Schedule	CP2
GTIN	785901583677
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.10 in (2.794 cm)
Package 1 Width	2.40 in (6.096 cm)
Package 1 Length	2.30 in (5.842 cm)
Package 1 Weight	2.24 oz (63.503 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------