

CHERRY KC 4000



Models may vary from the image shown

Flat compact keyboard for professional use

CHERRY KC 4000 is advanced CHERRY technology in a compact size.
Modern, flat compact design with soft and quiet keys.
Lasting, reliable and optimised for professional use.

Key benefits

- Flat and compact professional keyboard with quiet, short stroke keys
- Scissor technology: Up to 10 million key actuations
- Adjustable cable routing from the casing (left/centre/right)
- Plug & Play via USB connection
- Energy-saving technology
- Optimised for professional use in the office
- Two-tone key labelling

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing colour:

black

Key colour:

black

Weight (product):

345 g

Total weight (with packaging):

approx. 488 g

Cable Length:

approx. 1.80 m

Storage Temperature:

-20°C to 65°C

Operating Temperature:

0°C to 40°C

Current Consumption:

typ. 50 mA

Interface:

- USB

Product approvals:

- c-tick
- UL
- CE
- FCC



System requirements:

- USB connection

Delivery Volume:

- CHERRY KC 4000
- Operating instructions in hard copy

Dimensions (product):

305 x 146 x 15 mm

Packaging dimensions:

350 x 193 x 25 mm

Reliability:

- MTBF (90) > 80,000 hours

Keyboard:

- Key technology: SX
- Service life, standard key: > 10 million key operations
- Inscription technology: Laser
- Inscription layout: Standard
- Number of Keys: 88

Packaging Unit:

- Number of products in the master package: 20
- Number of master packages per pallet: 24

Warranty:

2 years

Errors, technical changes and delivery possibilities excepted.
Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)
1	CHERRY KC 4000	JK-0700BE	4025112081705	Belgium
2	CHERRY KC 4000	JK-0700CH	4025112081699	Switzerland
3	CHERRY KC 4000	JK-0700DE	4025112078149	Germany
4	CHERRY KC 4000	JK-0700ES	4025112081675	Spain
5	CHERRY KC 4000	JK-0700EU	4025112078156	US English with EURO symbol
6	CHERRY KC 4000	JK-0700FR	4025112081682	France
7	CHERRY KC 4000	JK-0700GB	4025112081668	UK
8	CHERRY KC 4000	JK-0700IT	4025112081712	Italy
9	CHERRY KC 4000	JK-0700PN	4025112081729	Pan-Nordic