

## Certification Record

CUSTOMER	CLASS	FILE
Schaffner EMV AG	<u>2221-82</u>	044788-C-000
Nordstrasse 11	AUDIO AND VIDEO EQUIPMENT-EMI Filters - Certified to US Standards	
Luterbach, , 4542 Switzerland	<b>Refer to Class Description for program details</b>	

### TO THE REQUIREMENT OF UL STANDARD NO 1283

- EMI filter, Model FS5281-15-07 rated 210V ac 15A, 50/60Hz, 3 phase, -25°C to 40°C.
- EMI filter, Models FS5323-3-99, FS5323-3-99-1, 250V ac, 50/60Hz, 3A, -25°C to 40°C.
- EMI filter, Model FS5301-40-24, 250V ac, 40A, 0-60Hz, -25°C to 60°C.
- EMI filter, one unit contains 3 single phase filters (only two of the three filters can be used at the same time), Model FS5297-10-04, rated 200-240V, 50/60Hz, (2x) 8.5A, 0 to 40°C.
- EMI filter, Model Series FN3100, 520/300V ac. 50/60Hz, 35A up to 150A, 3 phases, -25°C to 50°C.
- EMI filter Model Series FS5565, FS5566, 440/250V ac, 50/60Hz, 35A up to 96A, 3-phases, -25°C to 40°C.
- EMI filter Model Series FN3258, 480/275V ac, 50/60Hz, 7A up to 180A, 3-phases, -25°C to 50°C.
- EMI filter Model Series FN5864, 480/275V ac, 50/60Hz, 7A up to 180A, 3-phases, -25°C to 50°C.
- EMI filter Model FN5314-42-07, 480/275V ac, 50/60Hz, 42A, 3-phases, -25°C to 50°C.
- EMI filter Model FN5595-10-06, 250V, 0-60Hz, 10A, -25°C to 55°C.
- EMI filter Model Series FN6309, 440/250V ac, 50/60Hz, 36A up to 110A, 3-phases, -25°C to 40°C.
- EMI filter Model Series FN332, 250V, 50/60Hz, 0-60Hz, 1A up to 10A, -25°C to 40°C.
- EMI filter Model FS 5300-16-06-1, 48V, DC, 15A, -25°C to 40°C.
- EMI filter Model Series FN 2300, 250 V, 50/60Hz, 1A up to 20A, -25°C to 40°C.
- EMI filter Model FS 5309-3-99. rated 96 V, DC, 3A, -25°C to 50°C.
- EMI filter Model Series FN 9221, 250V, 50/60Hz, 1A up to 10A, -25°C to 40°C.
- EMI filter Model FS 5974-16-06-3, 250V, 50/60Hz, 16A, -25°C to 55°C.
- EMI filter Model FS 5280-6-07-1, 250V, 50/60Hz, 6A, -25°C to 40°C.
- EMI filter Model FS 5882-3-05, 520V ac, 50/60Hz, 3A, 3-phases, -25°C to 55°C.
- Series FN351H, 520V, 50-60Hz, Models FN351H-8-29, 8A; FN351H-16-29, 16A; FN351H-25-33, 25A;
- FN351H-36-33, 36A; FN351H-50-33, 50A; FN351H-64-33, 64A; FN351H-80-34, 80A; FN351H-110-35, 110A.
- Series FN354, 250/440V, 50-60Hz, Models FN354-4-xx, 4A; FN354-6-xx, 6A; FN354-12-xx, 12A; FN354-15-47, 15A; FN354-25-47, 25A.

Note: Certified as a component of Certified equipment where the suitability of the combination is to be determined by the Canadian Standards Association.