

# vacuum suction cup ESV-50-SN

Part number: 190994

FESTO

Wearing part, easily replaceable



## Data sheet

Feature	Value
Min. workpiece radius	330 mm
suction cup diameter	50 mm
suction cup volume	2.387 cm <sup>3</sup>
Position of connection	on top
Assembly position	Any
Suction cup shape	round flat
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
Food-safe	See Supplementary material information
Ambient temperature	-10 ... 70 °C
Retention force at nominal operating pressure	105 N
Product weight	11.2 g
Colour	Black
Shore hardness	60 +/- 5
Materials note	Free of copper and PTFE Conforms to RoHS
Material suction cup	NBR