

Circular Saw XGT®

HS004G

40V max • 6 000 min⁻¹ • 190 / 185 mm

Highly robust circular saw for demanding applications

40V max XGT® Li-ion battery and brushless motor makes this saw excellent choice for demanding applications. High cutting performance and compatible with guide rail without adapter.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	6000 min ⁻¹
Max. Cutting Depth at 90°	60 / 62,5 mm
Max. Cutting Depth at 48°	42 / 41 mm
Max. Cutting Depth at 45°	44,5 / 43 mm
AWS ready	✓
Sound Power Level (L _{WA})	104 dB(A)
Sound Pressure Level (L _{pA})	96 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Product Dimensions (L x W x H):	337 x 210 x 290 mm
Tool weight with battery	4,4 - 5,6 kg

User benefits

- Battery protection circuit protects against overloading, over-discharging and over-heating
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Brushless maintenance-free and long-life motor
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Compatible with guide rail without adapter
- Electric brake for maximum productivity and increased operator safety
- Magnesium components create lightweight saws that are well-balanced and job site tough
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work

Link to product - www.makitauk.com



Related products

Optional AC

164095-8

Parallel Guide

196520-1

Dust Nozzle

199140-0

Guide rail, 1 000 mm

B-64191

Circular Saw Blade, Efficut, TCT,

E-05670

Guide Rail Protective Holder



194367-7

Guide rail, 3 000 mm



198885-7

Guide rail joint connector set, 2 pcs



783204-6

Hex Wrench 6Mm



E-05664

Guide Rail Protective Holder



Other

User manual

Parts drawing