

# RS Pro 2, 3, 4 & 5 WAY M12 IN LINE PUSH-PULL CABLE PLUGS



## Specifications:

From RS Pro, these push-pull plugs are serious contenders for your application. The convenient push-pull connection, makes it perfect in situations where accidental disconnects occur. That coupled with the IP67 rating, makes sure that this industrial connector excels in harsh environments. When choosing a male connector, this version should really be one you consider.

|                          |   |
|--------------------------|---|
| Coupling Type            | Push and Pull                                   |
| IP Rating                | IP67  |
| Material                 | Metal   |
| Shell                    | Brass with chrome plating                       |
| Insert Material          | PPS max temperature 260°C, fire resistance: V-0 |
| Contact Material         | Brass with gold plating                         |
| Termination              | Solder  |
| Cable out diameter range | I: 4-6mm  |
| Mating cycle             | >500  |
| Temperature range        | -40°C~+85°C                                     |
| Insulation resistance MΩ | 2000  |