



Part Number : [194360413](#)

Product Description : MX150L 4 Circuit Rear Mount Flange Sealed Panel Mount Plug for 12-10 AWG Wire, without Gasket, Black

Series Number : 19436

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[194360413 sd.pdf](#)

[PK-19436-001-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-19432-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	19436
Description	MX150L 4 Circuit Rear Mount Flange Sealed Panel Mount Plug for 12-10 AWG Wire, without Gasket, Black
Application	Power, Wire-to-Wire
Comments	Mat Seal Color Yellow, Polarized to Mating Part; IP67 rated; Conforms to UL 1977; NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Product Name	MX150L
UPC	800756731865

Physical

Circuits Detail	2x2
Circuits (maximum)	4
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No

Keying to Mating Part	N/A
Lock to Mating Part	Yes
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	7.62mm
Pitch - Termination Interface	7.62mm
Polarized to Mating Part	No
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX150L Receptacle Housings	<u>19432</u>