

## FloorPro Multi Cleaner RM 756

Highly concentrated everyday cleaner for floors and surfaces. With a high-wetting formulation for maximum cleaning performance and an intensely fresh fragrance.

**pH 9**  
in concentrate



### Properties

- Everyday cleaner for all water-resistant hard and resilient floors and surfaces
- Very economical due to low dose of 0.25% to 1%
- Powerful cleaning performance thanks to high wetting capability
- Quick-drying
- Streak-free cleaning
- Low-foam formulation
- Gentle and ecofriendly
- Tensides biodegradable in accordance with OECD

### Usage options

- Scrubber driers
- manual

### Application areas

<b>Hotels, gastronomy, catering</b>	Floor and surface cleaning
<b>Nursing and retirement homes, doctor's surgeries</b>	Floor and surface cleaning
<b>Building cleaning</b>	Floor and surface cleaning
<b>Retail</b>	Floor and surface cleaning
<b>Municipal</b>	Floor and surface cleaning

### Technical data

Container sizes	Packaging unit	Part number
1 l	12 Piece(s)	6.295-913.0
2.5 l	4 Piece(s)	6.295-915.0
10 l	1 Piece(s)	6.295-914.0

## Application

### Scrubber driers

- Remove coarse dirt by sweeping.
- Use appropriate brush/roller/pad and squeegee for scrubber drier as required.
- Dose the product with clean water accordingly.
- Wet surface evenly with product (using brush/roller/pad as required).

### manual

- Remove coarse dirt by sweeping.
- Dose the product with clean water accordingly.
- Clean surface manually.

## Instructions for use

- Do not apply to water-sensitive surfaces.
- Do not apply to wood or unsealed parquet flooring.
- Shelf life: 4 years

## Warnings and safety recommendations according to EC Directives

- EUH 210 Safety data sheet available on request.

## Further information

- Material Safety Data Sheet (MSDS)

## Dosage and yield

Contents	Cleaning method	Dosage	Soiling	Yield
1000 ml	Manual - maintenance cleaning	0.25 - 1 %	light-medium	12000 - 20000 m <sup>2</sup>
1000 ml	Scrubber driers - maintenance cleaning	0.25 - 1 %	light-medium	12000 - 20000 m <sup>2</sup>