



(2.54 mm) .100"

**SMH SERIES** 

## **SMT HORIZONTAL SOCKET**

#### Mates With:

TSW, MTSW, MTLW, EW, ZW, TSS, ZSS, TSM

#### **SPECIFICATIONS**

For complete specifications and recommended PCB layouts see www.samtec.com?SMH

Insulator Material: Black LCP

Contact Material: Phosphor Bronze

Phosphor Bronze
Plating:
Au or Sn over
50 µ" (1.27 µm) Ni
Operating Temp Range:
-55 °C to +125 °C with Gold
-55 °C to +105 °C with Tin Insertion Depth:

(3.68 mm) .145" to (6.35 mm) .250"

Max Cycles: 100 with 10 µ" (0.25 µm) Au RoHS Compliant:

#### **PROCESSING**

Lead-Free Solderable:

SMT Lead Coplanarity: (0.15 mm) .006" max (02-24) (0.20 mm) .008" max (25-36)\* \*(.004" stencil solution may be available; contact IPG@samtec.com)

### RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



#### **ALSO AVAILABLE** (MOQ Required)

Other platings

# Important Note: SMH mated to TSM-DH/-SH not coplanar, SSM-DH/-SH recommended for coplanar

applications.

Some lengths, styles and options are non-standard, non-returnable.



