




Brand of **NTN corporation**



Technical data

51110

One direction thrust ball bearings



VISUAL (S)



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

Brand	SNR
d - Internal diameter	50 mm
D - External diameter	70 mm
D1 - Inner diameter outer ring	52 mm
d1 - External diameter inner ring	70 mm
T - Thrust bearing height	14 mm
rs - Min fillet radius	0,6 mm
Mass	0,139 kg

PRODUCT PERFORMANCE

Ca - Dynamic axial load rating	28800000 mN
C0a - Static axial load rating	75500000 mN
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	12 Hz
BPFI - Over rolling frequency on inner (60 rpm)	12 Hz
BSF - Over rolling frequency on rolling element (60 rpm)	8.398 Hz
BRF - Rotational frequency - rolling element (60 rpm)	4.199 Hz
FTF - Rotational frequency - cage (60 rpm)	0.5 Hz

ABUTMENT

ra max - Max shaft & housing fillet radius	0,6 mm
Da max - Max shoulder diameter OR	58 mm
da min - Min shoulder diameter IR	62 mm



51110

One direction thrust ball bearings



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

Page 3/3