

233.50.100 40 bar 1/2 NPT lower mount

Bourdon Tube Pressure Gauges, Stainless Steel

Item number:	9021140	
Quantity:	1 pcs.	
Order code:	233.50-E-BG440Z-ND-UZHZCZZ-ZZZZZZZ IZZZZZZ12ZZZ LABEL-PG1DE-ZZZZZ	213D3AZIYG0 ZZZ-
Overview:	233.50.100 40 bar 1/2 NPT lower mount Measuring System 316L Ingress protection: IP 65 class 1.0 Window: laminated safety glass Case filling fluid: glycerine Permissible ambient temperature: -20 ... +60 °C Permissible medium temperature: + 100 °C Pressure Gauge Standard: International (standard Europe) *WIKA* with Serial number Label: WIKA standard without / with Tag-number	
Details:	Bourdon Tube Pressure Gauges, Stainless Steel Series Model: 233.50 Specifications according to data sheet: PM 02.02 Measuring system: stainless steel Case filling: with Nominal size: 100 mm Scale range: 0...40 bar Process connection: 1/2 NPT Connector location: lower mount Window: laminated safety glass Pointer: standard pointer Accuracy class: class 1.0 Overpressure safe: standard Case material: Stainless steel 1.4301 Case surface: bare Material pressure element: Measuring System 316L Case filling fluid: glycerine Ingress protection: IP 65 Permissible medium temperature: + 100 °C Permissible ambient temperature: -20 ... +60 °C Movement: stainless steel Packaging: single packing Pressure Gauge Standard: International (standard Europe)	

Date: 24/01/2024



Manufacturer logo: *WIKA*
with Serial number