

Features

- Rated 10A
- Cat III (600V)
- Cat II (1000V)
- Opens 25mm

RS PRO Crocodile Clip 10A, Red

RS Stock No.: 0802807, 0802808, 0802809,
0802810



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These robust crocodile clips are EN 61010-1 compliant and feature CAT III (600V) CAT II (1000V) ratings, making them ideal for testing in a range of applications. With a 4mm socket at rear that accepts a shrouded plug or unshrouded probe, these crocodile clips are suitable for use with a wide range of multimeter test leads. This range of RS PRO crocodile clips also feature a 10A rating and opening jaw width of 25mm. Applications: Automotive, Industrial, Laboratory, Education.

General Specifications

Connector Type	Crocodile clip
Colour	See Table
Insulated	Yes

Mechanical Specifications

Jaw Opening	25mm
-------------	------

Electrical Specifications

Current Rating	10A
Cat Rating	Cat III (600V), Cat II (1000V)

Approvals

Declarations	RoHS
Standards Met	EN61010-1

Similar Products

Stock No.	Brand	Product Name	Colour
0802810	RS PRO	Crocodile Clip	Yellow
0802807	RS PRO	Crocodile Clip	Green
0802808	RS PRO	Crocodile Clip	Blue
0802809	RS PRO	Crocodile Clip	Brown
1873805	RS PRO	Crocodile Clip	1x Black, 1x Red

