



ENGLISH

Datasheet

RS Pro Pro 100W Mini High Bay

RS Stock No: 176-8523



This RS Pro 100W LED Mini High Bay is ideal for industrial and commercial applications such as factories and warehouses. It is a suitable replacement for 250W HID Fittings and comes with an integral Driver and flicker free technology. It also comes supplied with a hanging hook and 2m of power flex.



ENGLISH

Typical Properties

| | |
|--------------------|------------------------|
| Material | Aluminium |
| Wattage | 100 W |
| Beam Angle | 90° |
| Lumen Output | 11,000 Lm |
| Lumen Efficiency | 110 Lm/W |
| Lamp Type | Fixed LED |
| Voltage | 220-240 V AC / 50-60Hz |
| Colour Temperature | Cool White |
| CCT | 4000K |
| IP Rating | IP65 |
| IK Rating | IK08 |
| Rated Life | 30,000hrs |

