

**A-series
AEP DT 2.5 4C**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com

**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

Type	AEP DT 2.5 4C
Order No.	1989980000
Version	A-series, End plate
GTIN (EAN)	4050118374490
Qty.	50 pc(s).

Data sheet

A-series AEP DT 2.5 4C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	2.1 mm	Width (inches)	0.083 inch
Height	94.25 mm	Height (inches)	3.711 inch
Depth	29.1 mm	Depth (inches)	1.146 inch
Net weight	2.783 g		

Temperatures

Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	Wemid	Colour	Dark Beige
UL 94 flammability rating	V-0		

System specifications

Version	End plate
---------	-----------

Additional technical data

Snap-on	Yes	With snap-in pegs	Yes
---------	-----	-------------------	-----

Classifications

ETIM 6.0	EC000886	eClass 6.2	27-14-11-33
eClass 9.1	27-14-11-33		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S