



1150 Protector

Sensitive equipment needs protection, and since 1976 the answer has been the Peli™ Protector Case. These cases are designed rugged, and travel the harshest environments on earth. Against the extreme cold of the arctic or the heat of battle, Peli cases have survived. Made in the USA, these tough cases are designed with an automatic purge valve, that equalizes air pressure, a watertight silicone O-ring lid, over-molded rubber handles and stainless steel hardware.

- **Watertight, crushproof, and dustproof**
- Automatic pressure equalization valve - balances interior pressure, keeps water out
- O-ring seal
- Open cell core with solid wall design - strong, light weight
- Pick N Pluck™ with convoluted lid foam
- Peli's legendary lifetime guarantee**
- * Where applicable by law



CONFIGURATIONS



1150
Standard



1150NF
No Foam



1150WF
With Foam

DIMENSIONS

Interior (L×W×D)	8.29 x 5.79" x 3.75 (21.1 x 14.7 x 9.5 cm)
Exterior (L×W×D)	9.44 x 7.80" x 4.29 (24 x 19.8 x 10.9 cm)
Lid Depth	0.75" (1.9 cm)
Bottom Depth	2.87" (7.3 cm)
Total Depth	3.62" (9.2 cm)
Int Volume	0.1 ft³ (0.003 m³)
Padlock Hole Diameter	0.19" (0.5 cm)

MATERIALS

Body	Polypropylene
Latch	Polypropylene
O-Ring	Polymer
Pins	Stainless Steel
Foam	1.3 lb Polyurethane
Purge Body	ABS
Purge Vent	3 Micron Hydrophobic Non-Woven

COLOURS

 Black	 Blue	 Orange	 Silver
 Yellow			

WEIGHT

Weight With Foam	1.75 lbs (0.8 kg)
Weight Empty	1.61 lbs (0.7 kg)
Buoyancy	8.00 lbs (3.6 kg)
Master Pack Weight	13.95 lbs (6.3 kg)

TEMPERATURE

Minimum Temperature	-40°F (-40 °C)
Maximum Temperature	210°F (98.9 °C)

CERTIFICATIONS

IP67	
Def Stan 81-41	

OTHER

Master Pack	6
Military	yes

ACCESSORIES

 1151 3 pc. Replacement Foam Set	 1153 Replacement O-ring	 1150PF Special Application Panel Frame	 1507 Quick Mounts - set of 4	 1506TSA TSA Lock
 1500D Desiccant Silica Gel				