



Product Datasheet

ENGLISH

75mm Swivel Castor with Grey Rubber Tyred Wheel, 70kg load capacity



Specification	
Application	General Purpose / Industrial
Features	Ball Bearing Swivel Head
Fixing Centres	55x42mm
Fixing Centres Length	55mm
Fixing Centres Width	42mm
Fixing Hole Size	8mm
Fixing Plate Dimensions	75x60mm
Fixing Plate Length	75mm
Fixing Plate Width	60mm
Hub Bearing Type	Plain
Hub Material	Polypropylene
Load Capacity	70kg
Number of Fixing Holes	4
Overall Height	95mm
Rotation	Swivel
Tyre Material	Grey Rubber Tyre
Weight Class	Light Duty
Wheel Diameter	75mm
Wheel Width	25mm