



# 97 71 180


## Crimping Pliers for end sleeves (ferrules)



- Also as VDE version
- Easy crimping due to optimised transmission ratio
- Light and slim design
- For crimping end sleeves (ferrules) according to DIN 46228 parts 1 + 4 from 0.25 to 16 mm<sup>2</sup>
- Crimping in marked half-round dies for reliable connections between the sleeve and the conductor
- 9 particularly deep dies with conical side faces
- Special tool steel, forged, oil-hardened



<b>Article No.</b>	97 71 180
<b>EAN</b>	4003773054009
<b>Head</b>	polished
<b>Handles</b>	plastic coated
<b>Applications</b>	End Sleeves (ferrules)
<b>Capacity in square millimetres mm<sup>2</sup></b>	0,25 - 16,0
<b>Number of crimping positions</b>	9
<b>AWG</b>	23 - 5
<b>Length mm</b>	180
<b>Net weight g</b>	205



*technical change and errors excepted*

