

Datasheet

6241-0001 Compact IP67 Footswitch 4561701

- Medically approved - IEC 60601-1 and UL 60601-1
- Low profile tactile switch
- Lightweight operation, designed to withstand heavy loads
- Black flat top bellows footswitch / palm switch
- Single pole normally open contacts
- Back entry cable, base fitted with M4 inserts
- Supplied with 2 metres of 2 core black cable
- Sealed to IP67
- 50mA 24 V DC (Resistive)
- Operating Temperature: -5°C to +40°C



Outline Dimensions

