

| Attribute | Model Code | Value |
|-----------|-----------------------------------|-----------------------|
| | | LS22A336NHUXXU |
| | Screen Size (Class) | 22 |
| | Flat / Curved | Flat |
| | Active Display Size (HxV) (mm) | 478.656x260.28 |
| | Screen Curvature | N/A |
| | Aspect Ratio | 16:09 |
| | Panel Type | VA |
| | Brightness (Typical) | 250 cd/m ² |
| | Peak Brightness (Typical) | N/A |
| | Brightness (Min) | 200 cd/m ² |
| | Contrast Ratio Static | 3000:1(Typical) |
| | Dynamic Contrast Ratio | Mega |
| | HDR(High Dynamic Range) | N/A |
| | HDR10+ | N/A |
| | Resolution | 1,920 x 1,080 |
| | Response Time (ms) | 5(GTG) |
| | Viewing Angle (H/V) | 178°/178° |
| | Color Support | Max 16.7M |
| | Color Gamut (NTSC) | 72% |
| | Color Gamut (DCI Coverage) | N/A |
| | sRGB Coverage | N/A |
| | Adobe RGB Coverage | N/A |
| Display | Frame Rate | Max 60Hz |
| | Samsung MagicRotation Auto | N/A |
| | Eco Saving Plus | N/A |
| | Eco Motion Sensor | N/A |
| | Eco Light Sensor | N/A |
| | 0.00 W Off mode | N/A |
| | Eye Saver Mode | Yes |
| | Flicker Free | Yes |
| | Picture-In-Picture | N/A |
| | Picture-By-Picture | N/A |
| | Active Crystal Color | N/A |
| | Quantum Dot Color | N/A |
| | Game Mode | N/A |
| | Image Size | N/A |
| | USB Super Charging | N/A |
| | Daisy Chain | N/A |
| | Windows Certification | Windows 10 |
| | FreeSync | N/A |
| | G-Sync | N/A |
| | Off Timer Plus | N/A |
| | Smartphone Wireless Charging | N/A |
| | Screen Size Optimizer | N/A |
| | Black Equalizer | N/A |
| | Low Input Lag Mode | N/A |

| | | | |
|--|---------------------------------------|-----------------------|-----|
| General Feature | Refresh Rate Optimizor | N/A | |
| | Custom Key | N/A | |
| | Super Arena Gaming UX | N/A | |
| | HDMI-CEC | N/A | |
| | Auto Source Switch | N/A | |
| | Auto Source Switch+ | N/A | |
| | Adaptive Picture | N/A | |
| | USB-C Power Boost | N/A | |
| | Ultrawide Game View | N/A | |
| | Smart Type | N/A | |
| | Operating System | N/A | |
| | Bixby | N/A | |
| | TV Plus | N/A | |
| | Universal Guide | N/A | |
| Smart Service | SmartThings App Support | N/A | |
| | SmartThings | N/A | |
| | Mobile to Screen - Mirroring, DLNA | N/A | |
| | Tap View | N/A | |
| | Workspace | N/A | |
| | Sound Mirroring | N/A | |
| | ConnectShare™ (USB 2.0) | N/A | |
| | Wireless Display | No | |
| | D-Sub | 1 EA | |
| | DVI | No | |
| | Dual Link DVI | No | |
| | Display Port | No | |
| | Display Port Version | No | |
| | Display Port Out | No | |
| | Display Port Out Version | No | |
| | Mini-Display Port | No | |
| | HDMI | 1 EA | |
| | HDMI Version | | 1.4 |
| | Audio In | No | |
| | Headphone | No | |
| | USB Ports | No | |
| | USB Hub Version | No | |
| USB-C | No | | |
| USB-C Charging Power | No | | |
| Thunderbolt 3 | N/A | | |
| Thunderbolt 3 Charging Power (Port 1) | N/A | | |
| Thunderbolt 3 Charging Power (Port 2) | N/A | | |
| Ethernet (LAN) | N/A | | |
| WiFi | N/A | | |
| Interface | Bluetooth | N/A | |
| Audio | Speaker | No | |
| | Temperature | 10~40 °C | |
| Operation Conditions | Humidity | 10~80, Non-Condensing | |
| | | % | |

| | | |
|-------------|-------------------------------------|------------------------------|
| | Factory Tuning | N/A |
| Calibration | Built in Calibration Engine | N/A |
| | LUT(Look-up Table) Bit Depth | N/A |
| | Gray Balance | N/A |
| | Uniformity Correction | N/A |
| | Color Mode | N/A |
| | CMS(Color Management Software) | N/A |
| | Factory Calibration Report | N/A |
| | Color | BLACK |
| | Stand Type | SIMPLE |
| | HAS(Height Adjustable Stand) | N/A |
| Design | Tilt | -5.0° (±2.0°) ~21.0° (±2.0°) |
| | Swivel | N/A |
| | Pivot | N/A |
| | Wall Mount | 75.0 x 75.0 |
| | ENERGY STAR | N/A |
| Eco | Energy Efficiency Class | D |
| | Recycled Plastic | N/A |
| Power | Power Supply | AC 100~240V |
| | Power Consumption (Max) | 18 W |
| | Power Consumption (Typ) | 12.0 W |
| | Power Consumption (DPMS) | 0.30 W |
| | Power Consumption (Off Mode) | 0.30 W |
| | Power Consumption (Yearly) | 18 kWh/year |
| | Type | External Adaptor |
| | Set Dimension with Stand (WxHxD) | 504.4 x 365.5 x 179.9 mm |
| | Set Dimension without Stand (WxHxD) | 504.4 x 294.1 x 30.0 mm |
| | Package Dimension (WxHxD) | 565.0 x 110.0 x 350.0 mm |
| Dimension | Set Weight with Stand | 2.5 kg |
| | Set Weight without Stand | 2.2 kg |
| Weight | Package Weight | 3.6 kg |
| | Power Cable Length | 1.5 m |
| | D-Sub Cable | N/A |
| | DVI Cable | N/A |
| | HDMI Cable | Yes |
| | HDMI to DVI Cable | N/A |
| | DP Cable | N/A |
| | USB Type-C Cable | N/A |

| | | |
|------------|---------------------|-----|
| | Thunderbolt 3 Cable | N/A |
| | Mini-Display Gender | No |
| | Install CD | Yes |
| | Audio Cable | N/A |
| | USB 2.0 Cable | N/A |
| | USB 3.0 Cable | N/A |
| Accessory | Remote Controller | N/A |
| Disclaimer | Disclaimer | N/A |