



**Part Number :** [192880502](#)

**Product Description :** ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press

**Series Number :** 207125

**Status :** Active

**Product Category :** Crimp Presses and Crimp Hand Tools



---

## Documents & Resources

### Tooling Specifications

[ATS-192880502-001.pdf](#)

[TM-640160065-001.pdf](#)

[TM-640160065CN-001.pdf](#)

[TM-640160065DE-001.pdf](#)

[TM-640160065SP-001.pdf](#)

[TM-640160065FR-001.pdf](#)

[TM-640160065IT-001.pdf](#)

[TM-640160065JP-001.pdf](#)

[TM-640160065KR-001.pdf](#)

[TM-640160065MY-001.pdf](#)

[TM-640160065PL-001.pdf](#)

[TM-640160065RU-001.pdf](#)

[TM-640160065SK-001.pdf](#)

[TM-640160065TH-001.pdf](#)

[TM-640160065VN-001.pdf](#)

[TM-640160065TW-001.pdf](#)

[TM-192280498-001.pdf](#)

[TM-192280498SP-001.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
------------	--------------

EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207125
Description	ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press
Comments	The Crimp Tape Module 640162000 is a base unit that will work like an applicator in a Molex TM-3000 638017200, 638017300 industry standard crimp press or the Molex TM-4000 638017600 industry standard crimp press. The Crimp Tape Module will accept all ATP-301 and ATP-201 style crimp dies. This Crimp Tape Module will allow customers to process most of Molex's Mylar Tape product from 2

	AWG uninsulated and 4 AWG insulated products and up. The Crimp Tape Module will NOT work in any other industry standard crimp press or wire process machine. These ATP-301 style die sets can be used in the older style suitcase presses.
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Pneumatic Press
UPC	822350715102
Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>

## Mates With / Use With

### Use with Part(s)

Description	Part Number
Taped Terminal Crimp Module used with TM-3000 and TM-4000 presses with ATP-201 and ATP-301	<u>640162000</u>

die sets.	
Use With	Molex ATP-101 style presses

## Applicable Parts

Description	Part Number
InsulKrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 3/8" (M9), Length 34.30mm, Yellow, Tape	<u>190700154</u>
InsulKrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 5/16" (M8), Length 34.30mm, Yellow, Tape	<u>190700156</u>
Avikrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 1/4" (M6), Length 34.59mm, Yellow, Mylar Tape Carrier	<u>190730232</u>
Avikrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 1/4" (M6), Expanded Flare, Length 34.59mm, Yellow, Mylar Tape Carrier	<u>190730234</u>
Avikrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 3/8" (M9), Length 34.59mm, Yellow, Mylar Tape Carrier	<u>190730237</u>
Avikrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 3/8" (M9), Expanded Flare, Length 34.59mm, Yellow, Mylar Tape Carrier	<u>190730239</u>
Avikrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 5/16" (M8), Length 34.59mm, Yellow, Mylar Tape Carrier	<u>190730243</u>
Avikrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 5/16" (M8), Expanded Flare, Length 34.59mm, Yellow, Mylar Tape Carrier	<u>190730245</u>

InsulKrimp Ring Tongue Terminal for 16-14 AWG,	<u>190540127</u>
---------------------------------------------------	------------------

---

This document was generated on Sep 23, 2025