

## FEATURES

- **2.5 m cable length:** Offers flexibility and reach for diverse installations
- **IEC C15M to AS/NZS 3112 connectors:** Ensures compatibility with a wide range of devices
- **15 A current rating:** Supports high-demand electrical applications
- **250 V voltage rating:** Suitable for standard power requirements
- **Rubber jacket material:** Provides durability and resistance to wear
- **Black jacket colour:** Ideal for discreet installations
- **Straight mains socket type:** Facilitates straightforward connections

## RS PRO 2.5 m Power Cable, IEC C15M to AS/NZS 3112

RS Stock No: 558-965



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO power cable is designed for reliable electrical connections in various industrial and commercial settings. With a length of 2.5 metres, it provides flexibility and ease of use in connecting equipment to power sources. The cable supports a current rating of 15 A and a voltage of 250 V, making it suitable for high-demand applications.

## General Specifications

Connector Type A	IEC C15M
Connector Type B	AS/NZS 3112
Jacket Colour	Black
Mains Socket Type	Straight
Product Type	Power Cable

## Mechanical Specifications

Cable Length	2.5 m
Jacket Material	Rubber

## Electrical Specifications

Current Rating	15 A
Voltage	250 V

## Approvals

Standards/Approvals	CCCs, CSA, ENEC 11, JET, PSE, UL
---------------------	----------------------------------

