

JBL12-1



Sample image

Order symbol : JBL12-1

Product nr : 2550005

Description : Modular component enclosure, grey screw cover with inspection window, 1x13 modules

EAN : 6418074300140

El. number :

- Finland : 3424797
- Denmark : 8212010602
- Sweden : 2507763

Dimensions :	Height	Width	Depth
mm :	280	190	160
inch :	11.02	7.48	6.3

Materials :

Material :	Polycarbonate
Base colour :	RAL_7035
Cover colour :	Clear transparent
Gasket material :	Polyurethane

Ratings :

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK08;
electrical_insulation :	Not insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 746C
Flammability Rating :	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C :	960C

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175