

G-ESISEC-M20-S68N-NEPDS-S - Cable gland



1415163

<https://www.phoenixcontact.com/in/products/1415163>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: Brass, nickel-plated, application: Ex, external cable diameter 6 mm ... 13 mm, shielding: yes, connecting thread: M20 x 1.5, color: silver, with O-ring

Your advantages

- Dust protection during storage and transport provided by a dust cap.
- Weatherproof sealing material
- Halogen-free

Commercial data

Item number	1415163
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF7
Product key	AF7DDX
Catalog page	Page 651 (C-3-2019)
GTIN	4055626037943
Weight per piece (including packing)	59.24 g
Weight per piece (excluding packing)	59.24 g
Customs tariff number	74198090
Country of origin	DE

G-ESISEC-M20-S68N-NEPDS-S - Cable gland



1415163

<https://www.phoenixcontact.com/in/products/1415163>

Technical data

Mounting

Assembly note	Mounting the screw connection: - Mount cable gland support - Strip outer cable sheath. Expose around 7 mm of the cable shield. - Push the outer cone over the braided shield - Push the inner cone under the shield - Insert both, together with the cable, in the mounted screw connection support - Tighten union nut with the required torque
---------------	---


Product properties

Product type	Cable screw gland
Application	Ex
No. of conductors	1
Manufacturer	WISKA
Manufacturer Designation	EMSKE-L 20 EMV-Z
Shielded	yes

Ex data

Cable types that can be used	for unarmored cables
Suited for EX-applications	yes

Dimensions

Dimensional drawing	
Length	43 mm
Length of the connecting thread	12 mm
Hole diameter	20.1 mm ... 20.3 mm
Wrench size, union nut	24 mm
Wrench size, support	24 mm
Hexagon angular dimension	27 mm
Thread type connection side	M20 x 1.5
Thread pitch	1.5 mm

Connection data

Tightening torque	8 Nm (Support sleeve)
-------------------	-----------------------

Material specifications

G-ESISEC-M20-S68N-NEPDS-S - Cable gland



1415163

<https://www.phoenixcontact.com/in/products/1415163>

Color	Brass color
Material Compression ring	PA
Seal material Cable seal	EPDM
Material for screw connection	Brass, nickel-plated

Cable/line

External cable diameter	6 mm ... 13 mm
-------------------------	----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP68 (5 bar / 0.5 h)
Ambient temperature (operation)	-40 °C ... 75 °C (static)

Approvals

ATEX	II 2 G/D EEx e II IP68
IECEX	Ex e IIC Gb, Ex tb IIIC Db


G-ESISEC-M20-S68N-NEPDS-S - Cable gland



1415163

<https://www.phoenixcontact.com/in/products/1415163>

Drawings



G-ESISEC-M20-S68N-NEPDS-S - Cable gland



1415163

<https://www.phoenixcontact.com/in/products/1415163>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1415163>



cUL Recognized

Approval ID: E179850



UL Recognized

Approval ID: E179850



EAC Ex

Approval ID: RU C-DE.HA67.B.00120



GL

Approval ID: 20259-04 HH



IECEx

Approval ID: IECEx PTB 13.0027X



ATEX

Approval ID: PTB 04 ATEX 1112 X

cULus Recognized

G-ESISEC-M20-S68N-NEPDS-S - Cable gland



1415163

<https://www.phoenixcontact.com/in/products/1415163>

Classifications

ECLASS

ECLASS-11.0	27144432
ECLASS-12.0	27140801
ECLASS-13.0	27140802

ETIM

ETIM 9.0	EC000441
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	22d32485-5789-46ee-bfe3-354472f0564f

G-ESISEC-M20-S68N-NEPDS-S - Cable gland

1415163

<https://www.phoenixcontact.com/in/products/1415163>



Accessories

A-INLE-M20-N-S - EMC nut

1411269

<https://www.phoenixcontact.com/in/products/1411269>

EMC nut, for threads M20 x 1.5, color: silver



Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in