

Price* : 80.99 GBP



Main

| | |
|---------------------------|------------------------------|
| Range | ClimaSys |
| Product name | ClimaSys CR |
| Product or component type | Ultra thin resistance heater |
| Power range | 12 W |
| Input voltage | 240 V AC 50/60 Hz |
| Electrical connection | Cable length: 2 m |

Complementary

| | |
|---------------------------------------|--|
| Operating position | Horizontal Vertical |
| Ambient air temperature for operation | -60...70 °C |
| Temperature setting range | -40...70 °C |
| Material | Silicone rubber |
| Height | External: 110 mm |
| Width | External: 140 mm |
| Depth | External: 1.6 mm |
| Device composition | 6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts Fixing accessories |
| Condition of use | Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure |
| Fixing mode | By 4 screws |
| Mounting support | DIN rail Telequick mounting plate Adhesive Velcro Standard mounting plate |

Offer Sustainability

| | |
|------------------------|---|
| RoHS (date code: YYWW) | Compliant - since 1052 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
|------------------------|---|

| | |
|-------|--|
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
|-------|--|

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
