

## Data sheet

Commercial Art.No.: 83.040.1001.0

IP switch WIENET UMS 5-W

wienet IP switch. 5 Fast Ethernet ports with Auto MDI/MDI-X. Supports 10/100 Mbps Auto-Negotiation. Broadcast storm protection. Compact size with DIN-rail/Wall mount. Protection rate: IP30. Metal housing. Redundant 12 ... 48 V DC power input and P-Fail relay. Wide operating temperatures from -40 to 75°C (-40°F ... 167°F)



Commercial Art.No.	83.040.1001.0
EAN	4049088370939
Order Unit	1

## Technical data

### Allgemein

Mounting method	DIN rail (top hat rail)
Degree of protection (IP)	IP30
Housing material	Metal
Manageable	No
Ethernet	Yes
Power over Ethernet	No
Fast Ethernet	Yes
Gigabit Ethernet	No
Number of ports 10/100 Mbps RJ45	5
Diagnostic LEDs	P1, P2, P-Fail, 10/100T(x): Link/Activity, Duplex/Collision
10 Gigabit Ethernet	No
Number of ports 10/100/1000 Mbps RJ45	0
Number of ports 100 Mbps SC	0
Number of 100 Mbps ST-Ports	0

### Technical data

Voltage type	DC
Min. operating temperature	-40 °C
Max. operation temperature	75 °C
Redundant power supply	2 power inputs

### Supply circuit

Voltage type	DC
Operating voltage min.	12 V
Operating voltage max.	48 V
Power consumption max.	< 4.5 W

### Dimensions

Depth	95 mm
Width	30 mm

Height	120 mm
--------	--------

**Classification**

ECLASS 8.1	19170106
ETIM 7.0	EC000734
ETIM 6.0	EC000734
ETIM 5.0	EC000734
ETIM 4.0	EC000734
ETIM 3.0	EC000734