

## Han 24EMC/B-HBM-for DL



Image is for illustration purposes only. Please refer to product description.

Part number	09 62 824 2306
Specification	Han 24EMC/B-HBM-for DL
HARTING eCatalogue	<a href="https://harting.com/09628242306">https://harting.com/09628242306</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han <sup>®</sup> EMC/B
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	External seal
Type	Low construction

### Version

Size	24 B
Locking type	Double locking lever (on the hood)
Field of application	Hoods/Housings for higher EMC requirements

### Technical characteristics

Tightening torque	1 Nm Fixing screws M4
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP66
Type rating acc. to UL 50 / UL 50E	4 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated



**Pushing Performance**  
Since 1945

## Material properties

Colour (hood/housing)	Unpainted
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE
	DNV GL

## Commercial data

Packaging size	1
Net weight	106.786 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140172173
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466