



fitted with

work equipment

- connected load
- power consumption
- system of protection
- class of protection
- technology
- usage
- luminaire body
- lamp cover
- tubular sections
- balance of articulation joints
- weight (net)
- mains lead

fastening

- lens; dimensions
- lens; diopters
- add-on lens; dimensions
- special features

- 3 x compact fluorescent lamp TC-S 9W/840 G23
- light colour neutral white, 4000 K, Color Rendering Index (CRI)=85
- Energy efficiency category A
- conventional ballast
- Energy efficiency index (EEI): B2
- 230 V/ 50 Hz
- approx. 36 W
- IP 20
- I
- multi-stage switchable switch
- plastic, light grey
- screen, milky
- steel tube, painted, light grey
- spring
- approx. 4.5 kg
- approx. 3.0 m; mains plug
- CEE 7/VI
- screw-down flange, table clamp (accessory), wall bracket (accessory)
- 162 x 105
- 3
- not available
- light output controlled with 2-way-switch



CEE 7/VI

illuminance

measuring conditions: d=15cm

Em: 4252 lx
 Emax: 6096 lx
 Emin: 1967 lx

