

## FEATURES

- Ideal for precision work with soft wire
- Precision ground 3mm steel jaws
- Ribbed soft plastic grips and lightweight return spring
- Integral stop prevents handles opening too far

## RS PRO 146mm Steel Flat Nose Pliers With 16mm Jaw Length

RS Stock No.: 606-541



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

From RS PRO, these high-quality long nose pliers are suitable for professionals and enthusiasts alike. With rounded external edges, these smooth pointed pliers are suitable for the handling of components in high-density areas without causing damage.

### General Specifications

<b>Plier Type</b>	Flat Nose Pliers
<b>Tip Style</b>	Straight
<b>Material</b>	Steel
<b>Applications</b>	Electrical Work, Jewellery Making

### Mechanical Specifications

<b>Cutting Capacity</b>	3mm
<b>Jaw Length</b>	16mm
<b>Overall Length</b>	146mm
<b>Jaw Depth</b>	3mm
<b>Hardness</b>	HRC 48-50
<b>Weight</b>	78g
<b>Steel Thickness</b>	3.0mm

