

PRO Impact T Screwdriver Bit

PRO



- For driving T screws efficiently, eg when installing all types of panels, equipment, and fixtures
- Highly efficient for installers, electricians, metalworkers, and woodworkers: Robust
- Up to 50x more robust than a Bosch 2607001528 Extra Hard Bit
- 1/4" Impact rated Hex shank for use in impact driver and drill driver



PRODUCT PROPERTIES		ORDERING INFORMATION				
		Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number
T10, 25 mm, 2 pcs		PC1d	2	5	6949509233356	2 608 522 472
T15, 25 mm, 2 pcs		PC1d	2	5	6949509233349	2 608 522 473
T20, 25 mm, 2 pcs		PC1d	2	5	6949509233332	2 608 522 474
T25, 25 mm, 2 pcs		PC1d	2	5	6949509233325	2 608 522 475
T27, 25 mm, 2 pcs		PC1d	2	5	6949509233318	2 608 522 476
T30, 25 mm, 2 pcs		PC1d	2	5	6949509233301	2 608 522 477
T40, 25 mm, 2 pcs		PC1d	2	5	6949509233295	2 608 522 478
T20; T25; T30, 25 mm, 3 pcs		PC1d	3	5	6949509233288	2 608 522 479
T30, 25 mm, 8 pcs, with Pick and Click Index		PC1a	8	5	3165140912174	2 608 522 382
T15; T20(x2); T25(x2); T30(x2); T40, 25 mm, 8 pcs, with Pick and Click Index		PC1a	8	5	3165140851121	2 608 522 322
T20, 25 mm, 10 x 25 pcs, with Display		P1a	25	10	3165140980241	2 607 002 805
T25, 25 mm, 10 x 25 pcs, with Display		P1a	25	10	3165140980258	2 607 002 806
T30, 25 mm, 10 x 25 pcs, with Display		P1a	25	10	3165140980265	2 607 002 807
T10, 55 mm, 2 pcs		PC1d	2	5	6949509241979	2 608 522 528
T15, 55 mm, 2 pcs		PC1d	2	5	6949509241986	2 608 522 529
T20, 55 mm, 2 pcs		PC1d	2	5	6949509241993	2 608 522 530
T25, 55 mm, 2 pcs		PC1d	2	5	6949509242006	2 608 522 531
T30, 55 mm, 2 pcs		PC1d	2	5	6949509242013	2 608 522 532
T40, 55 mm, 2 pcs		PC1d	2	5	6949509242020	2 608 522 533
T10; T15; T20, 55 mm, 3 pcs		PC1d	3	5	6949509242037	2 608 521 U54
T25; T30; T40, 55 mm, 3 pcs		PC1d	3	5	6949509242044	2 608 521 U55
T15; T20(x2); T25(x2); T30(x2); T40, 55 mm, 8 pcs, with Pick and Click Index		PC1a	8	5	3165140851190	2 608 522 329
T25, 55 mm, 15 pcs, with Display		P1k	15	10	6949509242051	2 608 522 534
T20, 90 mm		PC1d	1	5	6949509242068	2 608 522 535
T25, 90 mm		PC1d	1	5	6949509242075	2 608 522 536
T30, 90 mm		PC1d	1	5	6949509242082	2 608 522 537