



Datasheet

Stock No: 481-349

ENGLISH

RS Pro 25m Extension Reel Type E - French, 4 Socket, Unwound Current Rating 16A IP44, Black



Product Details

4 socket reels with blanking caps - EURO

Open enclosure 25 m reel fitted with a circuit breaker.

The cable is made up of 3 H07RN-F 3G 1.5mm² conductors with black neoprene insulation.

Maximum power 3680 W.

The blanking caps ensure insulation to IP44.

Standards

Specifications:

| | |
|------------------------|-----------------|
| Reel Length | 25m |
| Socket Type | Type E - French |
| Number of Sockets | 4 |
| Current Rating Unwound | 16A |
| IP Rating | IP44 |
| Housing Type | Open Reel |
| Colour | Black |