

Number of contacts

92+

16 A 500 V 6 kV 3

Han E/
EE

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han® EE , Crimp termination, 1 ... 46</p> <p>Please order crimp contacts separately. You need two inserts for a complete assembly!</p>	0,14 ... 4	09 32 046 3001	09 32 046 3101	<p>1) distance for contact max. 21 mm</p>
<p>Han® EE , Continuing marking, Crimp termination, 47 ... 92</p> <p>Please order crimp contacts separately. You need two inserts for a complete assembly!</p>	0,14 ... 4	09 32 046 3011	09 32 046 3111	<p>104</p> <p>27</p> <p>14</p> <p>5</p> <p>35</p> <p>71</p> <p>95</p> <p>3,3</p> <p>M F</p> <p>Contact arrangement (view from termination side)</p> <p>Panel cut out</p>