









REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		RELEASED PER ECN-25-322737	21MAY2025	TR	RCG



Item	Description	Q'TY	Material
1	Shell	1 SET	ABS Black
2	Screws	2 PCS	Iron Alloy Nickel Plating
3	Screws	2 PCS	Iron Alloy Nickel Plating
4	Nut	2 PCS	Iron Alloy Nickel Plating
5	Screws	2 PCS	Iron Alloy Nickel Plating
6	Wire Clamp	2 PCS	Iron Alloy Nickel Plating
7	Shims	2 PCS	Iron Alloy Nickel Plating

A	B	C	D
53.3	43.8	8.2	46.6



CABLE DIAMETERS 8.0~10.0MM.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TARUN, R 02MAY2025																				
DIMENSIONS: mm		CHK NAIR, SREEKUMAR 03MAY2025																				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD RAGHAVAN, CG 03MAY2025	NAME D-SUB 44P BACKSHELL																			
<table border="1"> <tr><td>0 PLC</td><td>±</td><td>-</td></tr> <tr><td>1 PLC</td><td>±</td><td>0.40</td></tr> <tr><td>2 PLC</td><td>±</td><td>0.25</td></tr> <tr><td>3 PLC</td><td>±</td><td>-</td></tr> <tr><td>4 PLC</td><td>±</td><td>-</td></tr> <tr><td>ANGLES</td><td>±</td><td>-</td></tr> </table>		0 PLC	±	-	1 PLC	±	0.40	2 PLC	±	0.25	3 PLC	±	-	4 PLC	±	-	ANGLES	±	-	PRODUCT SPEC 108-161904	RESTRICTED TO	
0 PLC	±	-																				
1 PLC	±	0.40																				
2 PLC	±	0.25																				
3 PLC	±	-																				
4 PLC	±	-																				
ANGLES	±	-																				
MATERIAL		APPLICATION SPEC 114-161403	SIZE A2	CAGE CODE 00779																		
FINISH		WEIGHT -	DRAWING NO C=2508224	SCALE 1:1																		
		CUSTOMER DRAWING	SHEET 1 OF 1	REV A																		