



ENGLISH

Datasheet

Stock No: 672--425
RS Pro Lever Action Pump

Lever action pump with ZBH

SRL 840-35 I/min

Item number:

EAN:

13 042

4103810130427

Discount group:

A

Technical data

Delivery rate (l/stroke):

0,36

Delivery rate (I/min): Pumping media: 35 oils, up to SAE 50

Application:

container, for 60 / 200 / 220 I

Discharge:

through Perbunan discharge hose, 1000 mm,

with steel outlet

Length of suction tube (mm):

840

Lacquering:

silver

Barrel screw coupling:

G 2" male and M 64 x 4 male

Materials of parts in contact with liquid

Pump housing:

impact-resistant aluminium pressure die

casting

Seals:

NBR

Weight (kg):

2.8

Specification

- · Anti-kink spring and two hose clips
- Packed in single carton box

Notes

 For oils, up to SAE 50, self-lubricating, non-aggressive media, undiluted anti-freeze, fuel oil, diesel, petroleum

Packaging

Dimensions LxWxH (mm):

820 x 155 x 115

Weight including package (kg):

2.8

Packing unit:

1.0