



Main

Range of product	Odace
Product or component type	Rocker centre plate with LED
Device application	Switch
Product specific application	For RL and special loads
Light source	LED
Type of packing	Paint cover
Quantity per set	Set of 5

Complementary

Device mounting	Flush
Number of rocker	1
Fixing mode	Clip-in
Surface finish	Glossy
Material	PC: visor Thermoplastic ABS-UV stabilised: cover plate
Diameter	51 mm
Depth	8.5 mm
Net weight	0.005 kg
Targeted channel	Professional
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	EN 60669-1 2006/95/EEC
Product certifications	N[RETURN]NF
IK degree of protection	IK04
IP degree of protection	IP21D

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations