

# Product information

## 10.8V 1/4" LXT Drill Driver



Satisfying the professional's needs

### DF030DWE

Voltage	10.8 v
Drive shank Hex	1/4"
Max. in wood	21 mm
Max. in steel	10 mm
No Load Speed	H: 0 - 1300 / L: 0 - 350 rpm
Torque Settings	18+ drill
Torque Settings; S/H Nm	14/24
Battery Type	Lithium-ion
Battery Quantity (1.3Ah)	2
Vibration: Drilling	2.5 m/sec <sup>2</sup>
Vibration K factor	1.5 m/sec <sup>2</sup>
Noise sound pressure	70 dB(A)
Noise K factor	3 dB(A)



- Conveniently located push button for forward and reverse.
- High comfort grips.
- Lithium-ion batteries have greater life spans than their Ni-MH or Ni-Cad counterparts giving 430% greater run time.
- Two speed gear box.
- Ideal for applications in tight spaces.
- Keyless single sleeve hex chuck.
- LED job light.

Details correct as of: 8-10-2014

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

[www.makita.com](http://www.makita.com)