

5380905



# Pipe Cleaning Brush f/handle, 160 mm, Medium, White



Fits all Vikan-handles. Vikan's tube cleaner is effective for cleaning of various kinds of tubes. Suitable for cleaning of meat mincers in a butchery shop.

# Technical Data

Item Number	5380905
Visible bristle length	30 mm
Material	Polypropylene Polyester Stainless Steel
Suitable for Food Contact (EU 1935/2004), DoC <sup>1</sup>	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	12 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	960 Pcs
Quantity Per Layer (Pallet)	96 Pcs.
Box Length	380 mm
Box Width	290 mm
Box Height	175 mm
Product Diameter	90 mm
Length	160 mm
Width	90 mm
Height	90 mm
Gross Weight	0,171 kg
Net Weight	0,143 kg
Cubik metre	0,0013 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Gtin-13 Number	5705025380902
GTIN-14 Number (Box quantity)	15705025380909
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its

intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.