

# ME MAX 45 DKL TRANS - Housing cover



2901699

<https://www.phoenixcontact.com/gb/products/2901699>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Cover, width: 45.2 mm, height: 75.25 mm, depth: 5.5 mm, color: transparent



## Your advantages

- Easy, tool-free mounting

## Commercial data

Item number	2901699
Packing unit	10 pc
Minimum order quantity	30 pc
Sales key	ACHABZ
Product key	ACHABZ
GTIN	4046356150408
Weight per piece (including packing)	8.23 g
Weight per piece (excluding packing)	6.29 g
Customs tariff number	85369010
Country of origin	DE

# ME MAX 45 DKL TRANS - Housing cover



2901699

<https://www.phoenixcontact.com/gb/products/2901699>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Cover
Housing type	DIN rail housing
Housing series	ME-MAX
Product family	ME MAX 45..
Type	Cover
Ventilation openings present	no

### Dimensions

Width	45.2 mm
Height	75.25 mm
Depth	5.5 mm

### Material specifications

Color	transparent
Color (Housing)	transparent
Flammability rating according to UL 94	V2
CTI according to IEC 60112	250
Insulating material	IIIa
Housing material	PC
Surface characteristics	untreated

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	95 %

### PCB data

Type of PCB mount	Latching
-------------------	----------

# ME MAX 45 DKL TRANS - Housing cover



2901699

<https://www.phoenixcontact.com/gb/products/2901699>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2901699>



**UL Recognized**

Approval ID: E240868

# ME MAX 45 DKL TRANS - Housing cover



2901699

<https://www.phoenixcontact.com/gb/products/2901699>

## Classifications

### ECLASS

ECLASS-13.0	27190603
-------------	----------

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# ME MAX 45 DKL TRANS - Housing cover



2901699

<https://www.phoenixcontact.com/gb/products/2901699>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)