

Terminal strip marker carrier - KLM-A - 1004348

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Terminal strip markers, for strip marking, adjustable height, for use with end clamps E/UK, E/NS 35 N or CLIPFIX 35, lettering field size: 44 x 7 mm

The illustration shows a combination of versions KLM-A, and ESL 44 x 7

Why buy this product



Key commercial data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 017918 012038
Weight per Piece (excluding packing)	1.68 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	46 mm
Width (a)	9.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

General

Color	transparent
Components	free from silicone and halogen
Inflammability class according to UL 94	HB
Material	ABS
Marking mounting type	Plug in

Terminal strip marker carrier - KLM-A - 1004348

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Conductor marking

Insert label - EMT (44X7)R - 0819275



Insert label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK X, THERMOMARK S1.1, Mounting type: Insert, Cable diameter: 16-35 mm, Lettering field: 44 x 7 mm

Terminal marking

Insert strip - ESL 44X7 - 0808244



Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems, Plotter, Perforated, Mounting type: Insert, Lettering field: 44 x 7 mm

