



ENGLISH

Datasheet

RS Pro PET D-sub Connector Backshell, 37 Way

RS Stock No: **544-4405**



Product Details

RS Pro screwdown cover with jackscrews has 37 number of contact with C D-sub shell size in a PET housing. This straight screwdown cover is suitable for use with most standard and crimp D-connectors. This provides locking action with jack screws in combination with female screwlock assembly. The cover allows you for side or top cable entry through removable knockouts and cable retention.

Features and Benefits

- Cable to panel adapter system suitable for use with most standard and crimp D connectors
- Cover in black moulded Noryl to UL94V-0
- Offers locking action with jack screws in combination with female screwlock assembly
- Side or top cable entry via removable knockouts and cable retention
- Temperature of -20 to +75°C



ENGLISH

Specifications:

Body Orientation	Straight
Colour	Black
Housing Material	PET
Number of Contacts	37
Dimensions	53.1 x 73 x 16.3 mm
Operating Temperature Range	-20 to +75°C
Standards Met	UL 94V-0