



**Description:** • Bodies & trims manufactured from 316 stainless steel.


**B Series - Ball valves - A-LOK® Ended**

	Part number	Tube Outside Diameter
	<b>48</b> <small>Parker Direct Link</small>	4A-B6LJ2-SSP
	6A-B6LJ2-SSP	3/8"
	8A-B8LJ2-SSP	1/2"
	M6A-B6LJ2-SSP	6 mm
	M10A-B6LJ2-SSP	10 mm
	M12A-B8LJ2-SSP	12 mm


**C Series - Check valves (25 psi cracking pressure)**

	Part number	Tube Outside Diameter
	<b>51</b> <small>Parker Direct Link</small>	4A-C4L-25-SS
	6A-C6L-25-SS	3/8"
	8A-C8L-25-SS	1/2"
	M6A-C4L-25-SS	6 mm
	M10A-C6L-25-SS	10 mm
	M12A-C8L-25-SS	12 mm

**V Series - Needle valves - A-LOK® Ended**

	Part number	Tube Outside Diameter
	<b>49</b> <small>Parker Direct Link</small>	4A-V4LR-SS
	6A-V6LR-SS	3/8"
	8A-V8LR-SS	1/2"
	M6A-V4LR-SS	6 mm
	M10A-V6LR-SS	10 mm
	M12A-V8LR-SS	12 mm

**Gauge valves**

	Part number	Thread NPT
	<b>50</b> <small>Parker Direct Link</small>	HGVS8
	HLS2V	1/2

**HNVS Series - Needle valves**

	Part number	Thread NPT
	<b>50</b> <small>Parker Direct Link</small>	HNVS4FF
	HNVS8FF	1/2