

PRODUCT-DETAILS

TC92

SADDLE BASE .6X.6IN NAT NYL SCREW



General Information

Extended Product Type	TC92
Product ID	7TAG009910R0088
EAN	5414363059370
Catalog Description	SADDLE BASE .6X.6IN NAT NYL SCREW
Long Description	Saddle-Type Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 15.11mm (0.595 Inches), Width of 15.11mm (0.595 Inches), Height of 14.27mm (0.562 Inches), Screw Mounting Method, #6 Screw

Ordering

EAN	5414363059370
UPC	786210822389

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	5.1 in 130 mm
Package Level 1 Height	2.15 in 55 mm
Package Level 1 Depth / Length	7.35 in 187 mm
Package Level 2 Units	1000 piece
Package Level 2 Width	8.4 in 213 mm

Package Level 2 Height	7.7 in 196 mm
Package Level 2 Depth / Length	16.3 in 414 mm

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19680701
Material	Nylon/Polyamide 6.6
Mounting Holes	#6
Mounting Type	Screw
Number of Batteries	0
Process Temperature Rating	-40 to +185 °F
Product Name	PLASTIC MOUNTING BASE
Product Type	Mounting Base
Special Functions	Saddle Mounting Plate for use with round bundles.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC92
Instructions and Manuals	TC92

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

