

TORQUE SCREWDRIVERS

824 A

ISO 6789

PROMO



- Adjustable torque model for clockwise tightening, for use in combination with bits from the 660 series or, using an adapter, with sockets from the 1/4" manual series
- Accuracy $\pm 6\%$ of the preset torque value
- Readings in Nm
- Automatic disengagement on reaching the preset torque value
- Automatic resetting after 120°
- Supplied with regulation key and test certificate

Family details

Code	Capacity Nm	Resolution Nm	L mm	Quantity for packaging
U08240004	0,5÷2,5	0,1	145	1
U08240006	2÷10	0,5	167	1

Sets / Compositons

Articles



425 TPMS - Kit with 10 tools to assemble / disassemble the tyre valves with Tyre Pressure Monitoring System (TPMS)

Stanley Black & Decker Italia S.r.l.

Sede legale: Via Energy Park 6 - 20871 Vimercate (MB)
Sede operativa: Via Volta 3 - 21020 Monvalle (VA) Italia
Partita IVA e C.F.: 03225990138

StanleyBlack&Decker

Società a Socio Unico soggetta a coord. e controllo da parte di Stanley Black & Decker, Inc.
Capitale Sociale I.V. € 12.000.000

Articles




519 M 425TPMS - Bi-colour foam module with assortment (10 pcs.)



519 M 824SK11 - Bi-colour foam module with assortment (11 pcs.)



519 M 824SK13 - Bi-colour foam module with assortment (13 pcs.)



519 M 824SK23 - Bi-colour foam module with assortment (23 pcs.)



824 SK11 - Basic kit for replacement of cutting plates (11 pcs.)



824 SK13 - Basic kit for replacement of cutting plates (13 pcs.)



824 SK23 - Universal kit for replacement of cutting plates (23 pcs.)