




PCB LAYOUT



TECHNICAL CHARACTERISTICS

MATERIAL

INSULATOR MATERIAL: PBT
COLOUR: BLACK
CONTACT MATERIAL: COPPER ALLOY
CONTACT TYPE: STAMPED
CONTACT PLATING: GOLD
SHIELDING: BRONZE NI PLATED
QUALITY CLASS: 500 MATING CYCLES

ENVIRONMENTAL

OPERATING TEMPERATURE: -25 °C UP TO 85 °C
FLAMMABILITY RATING UL94-V0
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL

CURRENT RATING: 1.5 A
WORKING VOLTAGE: 125 VAC
INSULATION RESISTANCE: >1000 MOHM
DIELECTRIC WITHSTANDING VOLTAGE: 1 000 VAC/MN
CONTACT RESISTANCE: 20 MOHM MAX

SOLDERING

WAVE PROCESS ONLY

PACKAGING

TRAY

				PROJECTION:	GENERAL TOLERANCE .X = ± 0.2 .XX = ± 0.15		DESCRIPTION: RJ45 SHIELDED TAP UP	SIZE A4
G								
F				APPROVAL: RJ	UNIT: MM SCALE: SHEET: 1/1 DRAW:	WERI PART NO: 615008140621		
E								
D								
C								
B				APPROVAL: RJ	UNIT: MM SCALE: SHEET: 1/1 DRAW:	WERI PART NO: 615008140621		
A	03-FEB-07	PDF	CH					
REV	DATE	FILE	BY					